


# Calibration Columns with Top Slip Caps



NOTE: - USE ONE (1) MINUTE TEST TO DETERMINE FLOWRATE  
 - CALIBRATION COLUMNS ARE USED IN GRAVITY SYSTEMS OPEN TO THE ATMOSPHERE AND THEREFORE ARE NOT PRESSURE RATED

| MODEL       | "A"     | "B"  | "C"    | "D"   | "E"    | INCREMENTS         |
|-------------|---------|------|--------|-------|--------|--------------------|
| 100 ML-SC   | 12-1/2" | 1/2" | 1.315" | 1.5   | 100    | 1 ML / 0.020 GPH   |
| 250 ML-SC   | 16-1/4" | 1/2" | 1.660" | 4.0   | 250    | 2 ML / 0.050 GPH   |
| 500 ML-SC   | 16"     | 3/4" | 2.375" | 8.0   | 500    | 5 ML / 0.050 GPH   |
| 1000 ML-SC  | 25"     | 3/4" | 2.375" | 16.0  | 1,000  | 5 ML / 0.125 GPH   |
| 2000 ML-SC  | 24"     | 1"   | 3.500" | 32.0  | 2,000  | 10 ML / 0.250 GPH  |
| 4000 ML-SC  | 34"     | 1"   | 4.000" | 64.0  | 4,000  | 20 ML / 0.250 GPH  |
| 10000 ML-SC | 27"     | 2"   | 6.625" | 160.0 | 10,000 | 100 ML / 1.000 GPH |
| 20000 ML-SC | 46"     | 2"   | 6.625" | 320.0 | 20,000 | 100 ML / 1.000 GPH |

|  |              |                           |
|--|--------------|---------------------------|
| <b>Koflo Corporation</b><br>309 CARY POINT DR.<br>CARY, IL 60013 |              |                           |
| SCALE: NONE  | APPROVED BY: | DRAWN BY: N.J.F           |
| DATE: 2/6/07   |              | REVISED: 8/7/07           |
| CUSTOMER:  |              | REVISED: 11/24/10         |
|  |              | REVISED: 8/14/14          |
| MODEL NO:<br>PVC CALIBRATION COLUMNS WITH TOP SLIP CAPS          |              | DRAWING NUMBER<br>KD-1033 |